

# SOLUTIONS FOR YOUR GOODLIFE!

## **Teak wood door design mat for bathing safety IWS53322**

### **Features:**

1. Provide safety assurance while taking a shower.
2. Provide adequate balance by using many stripe.
3. Catch the ground with six supporting point.
4. Supply waterproof for long time.
5. The Anticorrosive Warrior.

### Product Features

<b>Product's name</b>	<b>Teak wood door design mat for bathing safety IWS53322</b>	<b>brand</b>	GoodLife
<b>Item number.</b>	IWS53322		
<b>colors</b>	Raw wood color		
<b>Function</b>	Bathing furniture.non-slip		
<b>Material</b>			
<b>Material function</b>	Waterproof, Anticorrosive		
<b>Product Size</b>			
<b>Package size</b>	53*35*3.5cm[20.87*13.78*1.38INCH]		
<b>Package</b>	Mail Order package for reship		
<b>Carton CBM</b>	0.014m <sup>3</sup> / set		
<b>20GP</b>	1500sets	<b>N.W. /G.W.</b>	
<b>40HQ</b>	3540sets	<b>MOQ</b>	200 PCS

### Design And Color



Goodlife  
Houseware Ltd

IWS53322

**Goodlife**  
Houseware Ltd



IWS53322



Goodlife  
Houseware Ltd

IWS53322

Goodlife  
Houseware Ltd



IWS53322



IWS53322

**Goodlife**  
Houseware Ltd



IWS53322

Workmanship And Package





## Material



VS



Particle board

## Certificates



## Our team



### **Our Business services:**

1. Your inquiry related to our products or prices will be replied in 12 hours in working date.
2. Experience sales answer your question and give you related business service.
3. OEM & amp; ODM are welcome, we have over 10 years experience working with OEM project.
4. We are looking for exclusive sales of ODM [Cabinet wooden mirror jewelry](#).
5. Sales The exclusive right agent sales have been protection.

### **Package information:**

1. Forming polyfoam for the post package
2. 6-side strong polyfoam are used for safety package during transportation.
3. assembled kit and user manual are available for each office.

### **production lead time**

1. 25 ~ 50 days after deposit received.
2. Normal in the production lead time production line is 15 days after deposit received.

Hot Selling

				
<b>GLD17047</b>	<b>GLD13315</b>	<b>GLD14740</b>	<b>GLD15315</b>	<b>GLD15347</b>

			
<b>GLD08012</b>	<b>GLD08055</b>	<b>GLD08057</b>	<b>GLD08067</b>





GLS11325WH



GLS18703BR



GLS18812TK



GLS18715WH